

# Product Specification PDF

Date	<b>Correct as of 21st May 2019</b>
Brand	<b>Kasp</b>
Product	<b>K13040D</b>
Description	<b>Laminated Padlock 40mm</b>
Barcode	<b>5013969900934</b>
Commodity code	<b>8301100000</b>
Country of origin	<b>CN</b>



## Features & Benefits

~ Hardened steel shackle ~ Double bolted locking mechanism ~ Zinc plated steel laminated body ~ 8 steel countersunk rivets ~ extra strength over traditional locks ~ 5 pin cylinder with anti pick mushroom pins ~ Paracentric keyway ~ Supplied with 2 keys ~ Padlock width: 40 mm ~ Shackle diameter: 7,1 mm ~ Internal shackle height: 21 mm

## Applicable Standards

### Health & Safety

None applicable

### Warranty

KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years. Fair wear and tear or Damage caused through inappropriate use or attempted break in is not covered.

## Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	6	36
Width mm	44	140	150	360
Depth mm	25	23	185	490
Height mm	65	170	100	160
Weight	224	253	1604	10.4
Packaging Information	Card use	Box	Box	Case
	Card gms	7	86	787.5
	Plastic use	Blister	0	-
	Plastic gms	22	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0