








Voltage (Max.)	32 VDC.	Mounting Holes	ATC Blade Fuse Isometric View
Output Terminal Rating	25A max. load per circuit.	Terminal Dim.	Blade Fuse Dim.
Terminal Wire Size	#10-16 AWG.		
Fuse Specifications	For ATC Blade Fuses Used Only		
Mounting Torque Rating	8 in-lb (0.9Nm) max.		
Environmental Rating	IP 56		
Temperature Rating	-25 ℃J to +85 ℃J		



Circuit Diagram



Material :
 Cover : PC. (Clear)
 Housing &. Base : PBT. (Black)
 Terminal : Copper

NOTE:
 Tolerance ± 0.5 except noticed
 For CEI

				Drawn	Checked	Approved	SCI BOM No.		Model Name	REAR TERMINAL ATC BLADE FUSE BLOCK (10P)
				曹盈芳			Customer No.		Model No.	R3-83-01-1L310
Date	Name	Description	NO	10/16/12			Unit	mm	Shin Chin Industrial Co., Ltd.	Rev. X2