





Rating	8A 125VAC, 4A 250VAC		Mounting Hole	Circuit Diagram
	10A 125VAC, 6A 250VAC 10A 28Vdc, 6A 14VT			
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1500V 1 minute		Thickness	
Operation Temperature	-25°C~85°C		0.75...1.25	19.2-0.1 7.0+0.1
Switch Function	2P SPST ON-OFF		1.25...2	19.4-0.1 7.0+0.1
			2...3	19.8-0.1 7.0+0.1



Material:
 Frame: Black, Nylon# 66
 Actuator: Black, Nylon# 66
 Printed: White, hot stamping

原稿
 RD
 原稿
 7/10/05-134

C8\R13\R13-243A-02(1821661)

Date		Name		Description		NO	
Drawn	Checked	Approved	SCI BOM NO.	1821661	Model Name	ROCKER SWITCH	
曹盈芳	<i>[Signature]</i>	<i>[Signature]</i>	Customer No.		Model No.	R13-243A-02	REV.
09/12/07	P/B/09	9/12/07	Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		0