

## Illuminated push button Ø 22 mm silver contact

82-6152.1114



<https://www.eao.com/component/82-6152.1114/en...>

Your product:

---



82-6152.1114  
Illuminated push button Ø  
22 mm silver contact

#### FRONT

|                       |                 |
|-----------------------|-----------------|
| Front dimension:      | Ø 25 mm         |
| Front form:           | Round           |
| Front bezel material: | Stainless steel |
| Front bezel shape:    | Flush           |

#### MOUNTING

|                   |                |
|-------------------|----------------|
| Mounting cut-out: | Ø 22 mm        |
| Mounting type:    | Panel mounting |

#### OPERATING-/INDICATION PART

|                        |                 |
|------------------------|-----------------|
| Lens colour:           | Silver          |
| Lens material:         | Stainless steel |
| Lens illumination:     | Illuminated     |
| Lens shape:            | Flush           |
| Lens optics:           | opaque          |
| Illumination colour:   | Red             |
| Shape of illumination: | Ring            |

#### ELECTRICAL CHARACTERISTICS

Switching voltage and switching  
current:

|                                                            |                     |
|------------------------------------------------------------|---------------------|
| according to IEC 60947-5-1 (Silver contacts)               |                     |
| Service categorie AC-15                                    |                     |
| Voltage                                                    | Current             |
| 24 VAC                                                     | 1 A                 |
| 35 VAC                                                     | 1 A (M12 version)   |
| 110 VAC                                                    | 1 A                 |
| 220 VAC                                                    | 0.5 A               |
| Switch rating DC service categorie DC-13 (Silver contacts) |                     |
| Voltage                                                    | Current             |
| 24 VDC                                                     | 0.7 A               |
| 35 VDC                                                     | 0.5 A (M12 version) |
| 110 VDC                                                    | 0.2 A               |
| 220 VDC                                                    | 0.1 A               |

|                                       |         |
|---------------------------------------|---------|
| according to UL 508 (Silver contacts) |         |
| cosφ 0,75 ... 0,8                     |         |
| Voltage                               | Current |
| 120 VAC                               | 5 A     |
| 240 VAC                               | 3 A     |
| 24 VAC                                | 1 A     |

|                                      |                                                            |
|--------------------------------------|------------------------------------------------------------|
| <b>Contacts:</b>                     | 1 C                                                        |
| <b>Operating voltage:</b>            | 24 V AC/DC                                                 |
| <b>Operation current:</b>            | 7 mA                                                       |
| <b>Rated Operational Voltage Ue:</b> | 250 VAC                                                    |
| <b>Rated insulation voltage Ui:</b>  | 250 V                                                      |
| <b>Switching rating:</b>             | 240 V @ 3 A                                                |
| <b>Electrical lifetime:</b>          | 50 000 cycles of operation                                 |
| <b>Electric strength:</b>            | 1500 VAC, 50 Hz 1 minute between life terminals and ground |
| <b>Pollution degree:</b>             | 2, according to EN IEC 60947-1                             |
| <b>Thermal current Ith:</b>          | 5 A                                                        |

## MECHANICAL CHARACTERISTICS

|                             |                               |
|-----------------------------|-------------------------------|
| <b>Terminal:</b>            | Screw terminal                |
| <b>Contact material:</b>    | Silver                        |
| <b>Switching action:</b>    | Momentary                     |
| <b>Switching system:</b>    | Snap-action switching element |
| <b>Mechanical lifetime:</b> | 500 000 cycles of operation   |
| <b>Operating force:</b>     | 4 N ... 7 N                   |
| <b>Operating Travel:</b>    | ca. 3 mm                      |
| <b>Tightening torque:</b>   | 0.5 ... 0.6 Nm                |
| <b>Weight:</b>              | 0.018 kg                      |


## AMBIENT CONDITION

|                               |                                                                |
|-------------------------------|----------------------------------------------------------------|
| <b>IP front protection:</b>   | IP65, IP67                                                     |
| <b>Operating temperature:</b> | – 30 °C ... + 70 °C                                            |
| <b>Storage temperature:</b>   | – 40 °C ... + 80 °C                                            |
| <b>Shock resistance:</b>      | Max. 500 m / s <sup>2</sup> as per IEC 60068-2-27              |
| <b>Vibration resistance:</b>  | 10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6 |
| <b>Climate resistance:</b>    | Damp heat, 21 days according to IEC 60512-11                   |

## CERTIFICATE

|                      |                                                 |
|----------------------|-------------------------------------------------|
| <b>Approbations:</b> | CB, CCC, C UL, UL                               |
| <b>Conformities:</b> | CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD) |
| <b>REACH:</b>        | REACH compliant                                 |
| <b>RoHS:</b>         | RoHS compliant                                  |


## OTHER

|                              |                                                                                                                                              |
|------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Short Description:</b>    | Illuminated push button Ø 22 mm silver contact, Momentary, 240 V @ 3 A, 24 V AC/DC, 1 C, Screw terminal, Round, Stainless steel, Red, Silver |
| <b>Kind of illumination:</b> | Single-LED                                                                                                                                   |
| <b>Wiring diagrams:</b>      |                                                          |


## Component layouts:



#### Mounting cut-outs:



#### Dimension drawings:



A = Solder terminal  
B = Screw terminal