


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® GMP-GL-M	12.09.2012

Glass fibre-reinforced for maximum mechanical stability
Supporting surface for spanner means scratches on the housing are avoided



Application range

For locking SKINTOP® cable glands in boreholes without thread.

Design

Metric connection thread acc. to EN 50262

Approvals (Norm references)

UL File Nr. E79903

Note

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
Designed for use with metric SKINTOP® plastic cable glands

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data


On request:	Available without collar (without surface for assembling tool)
Colour delivered:	Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant
Material:	Polyamide, glass fibre-reinforced
Temperature range:	Fixed: -40°C to +100°C Dynamic: -20°C to +100°C

Product Management	Document: LAPP_PRO998EN.pdf	1 / 3
--------------------	-----------------------------	-------

SKINTOP® GMP-GL-M

12.09.2012

Part number	Article designation / size	SW (mm)	Pieces / PU
SKINTOP® GMP-GL-M silver grey			
53119000	12 x 1,5	17	100
53119010	16 x 1,5	22	100
53119020	20 x 1,5	27	100
53119030	25 x 1,5	34	100
53119040	32 x 1,5	41	100
53119050	40 x 1,5	50	25
53119060	50 x 1,5	60	25
53119070	63 x 1,5	75	25
SKINTOP® GMP-GL-M black			
53119100	12 x 1,5	17	100
53119110	16 x 1,5	22	100
53119120	20 x 1,5	27	100
53119130	25 x 1,5	34	100
53119140	32 x 1,5	41	100
53119150	40 x 1,5	50	25
53119160	50 x 1,5	60	25
53119170	63 x 1,5	75	25
SKINTOP® GMP-GL-M light grey			
53119003	12 x 1,5	17	100
53119013	16 x 1,5	22	100
53119023	20 x 1,5	27	100
53119033	25 x 1,5	34	100
53119043	32 x 1,5	41	100
53119053	40 x 1,5	50	25
53119063	50 x 1,5	60	25
53119073	63 x 1,5	75	25

U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® GMP-GL-M	12.09.2012



Product Management	Document: LAPP_PRO998EN.pdf	3 / 3
--------------------	-----------------------------	-------