

U.I. Lapp GmbH	PRODUCT INFORMATION	 LAPP GROUP
	SKINTOP® DIX-M	12.09.2012

Easy insertion of several cables into one gland
Higher packing density allows smaller part construction



Application range

For use in SKINTOP® cable glands.

A sealing ring with several holes is used in place of the inner sealing insert.

Design

SKINTOP® DIX-M VITON® is resistant to oil, water, alkaline solutions, acids, solvents etc.

Note

IP 68 can be achieved when all openings are closed and all bores are optimally occupied, i.e. when using cables with nominal diameter and/or SKINTOP® DIX-DV sealing plugs


Remark

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

On request:	Special shapes
Colour delivered:	Black (RAL 9005)
Material:	NBR VITON®
Protection rating:	IP 54
Temperature range:	-40°C to +100°C



Product Management	Document: LAPP_PRO999EN.pdf	1 / 3
--------------------	-----------------------------	-------

SKINTOP® DIX-M

12.09.2012

Part number	Article designation / size	Size M	Number of cables x cable Ø	Pieces / PU
SKINTOP® DIX-M				
53316220	16220	M 16	2 x 2	100
53316230	16230	M 16	2 x 3	100
53316240	16240	M 16	2 x 4	100
53316420	16420	M 16	2 x 4	100
53320250	20250	M 20	2 x 5	100
53320260	20260	M 20	2 x 6	100
53320340	20340	M 20	3 x 4	100
53320353	20353	M 20	3 x 5,3	100
53320440	20440	M 20	4 x 4	100
53320920	20920	M 20	9 x 2	100
53320430	20430	M 20	4 x 3	100
53325260	25260	M 25	2 x 6	50
53325350	25350	M 25	3 x 5	50
53325360	25360	M 25	3 x 6	50
53325370	25370	M 25	3 x 7	50
53325450	25450	M 25	4 x 5	50
53325540	25540	M 25	5 x 4	50
53325640	25640	M 25	6 x 4	50
53332270	32270	M 32	2 x 7	50
53332280	32280	M 32	2 x 8	50
53332290	32290	M 32	2 x 9	50
53332370	32370	M 32	3 x 7	50
53332380	32380	M 32	3 x 8	50
53332460	32460	M 32	4 x 6	50
53332470	32470	M 32	4 x 7	50
53332560	32560	M 32	5 x 6	50
53332650	32650	M 32	6 x 5	50
53332840	32840	M 32	8 x 4	50
53332850	32850	M 32	8 x 5	50
53332940	32940	M 32	9 x 4	50
53340290	40290	M 40	2 x 9	25
53340310	40310	M 40	3 x 10	25
53340480	40480	M 40	4 x 8	25

Part number	Article designation / size	Size M	Number of cables x cable Ø	Pieces / PU
53340490	40490	M 40	4 x 9	25
53340580	40580	M 40	5 x 8	25
53340590	40590	M 40	5 x 9	25
53340670	40670	M 40	6 x 7	25
53340860	40860	M 40	8 x 6	25
53340969	40969	M 40	9 x 6,9	25
53350118	50118	M 50	11 x 8	10
53350680	50680	M 50	6 x 8	10
53350780	50780	M 50	7 x 8	10
53350870	50870	M 50	8 x 7	10
53350147	50147	M 50	14 x 7	10
53350164	50164	M 50	16 x 4	10
53350166	50166	M 50	16 x 6	10
SKINTOP® DIX-M VITON®				
53420250	20250	M 20	2 x 5	100
53420260	20260	M 20	2 x 6	100
53440969	40969	M 40	9 x 6,9	25