


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SILVYN® MPC-M	12.09.2012

All-purpose
Fast and easy assembly



Info
NEW!!!

Application range

In combination with protective conduit
SILVYN® SI/SP/SP-PU (smooth conduits)
SILVYN® EL/ELÖ/ELT (corrugated conduits)

Design

Metric connection thread
Hexagonal collar with integrated conduit connection

Approvals (Norm references)

UL FILENUMBER E308201

Product features

Dust protection
Moisture-protection
High-tensile

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

On request:	With 45° elbow Grey, RAL 7001
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 65
Temperature range:	-50°C to +135°C



Product Management	Document: LAPP_PRO141567EN.pdf	1 / 2
--------------------	--------------------------------	-------

Part number	Article designation	Connection thread M	Clear opening (mm)	Suitable for SILVYN® SI	SILVYN® EL/ELÖ/ELT
SILVYN® MPC-M black					
55502460	SILVYN MPC M16/1	16 x 1.5	8.0	11 x 14	10 x 14,7
55502461	SILVYN MPC M16/2	16 x 1.5	11.0	13 x 16	12 x 16,6
55502462	SILVYN MPC-M 20/1	20 x 1.5	14.0	13 x 16	12 x 16,6
55502463	SILVYN MPC M20/2	20 x 1.5	14.0		16 x 20,7
55502464	SILVYN MPC M25	25 x 1.5	19.0		22 x 27,7
55502465	SILVYN MPC M32/1	32 x 1.5	23.0		25,0 x 30,6
55502469	SILVYN MPC M16/1	M32 x 1.5	25.0		28 x 33,5
55502466	SILVYN MPC M40	40 x 1.5	33.0		35 x 41,0
55502467	SILVYN MPC M50	50 x 1.5	37.0		40 x 46,4
55502468	SILVYN MPC M63	63 x 1.5	48.0		50 x 57,2
SILVYN® MPC-M grey					
55502441	SILVYN MPC M16/1	16 x 1.5	8.0	11 x 14	10 x 14,7
55502442	SILVYN MPC M16/2	16 x 1.5	11.0	13 x 16	12 x 16,6
55502443	SILVYN MPC-M 20/1	20 x 1.5	14.0	13 x 16	12 x 16,6
55502444	SILVYN MPC M20/2	20 x 1.5	14.0		16 x 20,7
55502445	SILVYN MPC M25	25 x 1.5	19.0		22 x 27,7
55502446	SILVYN MPC M32/1	32 x 1.5	23.0		25,0 x 30,6
55502447	SILVYN MPC M16/1	M32 x 1.5	25.0		28 x 33,5
55502448	SILVYN MPC M40	40 x 1.5	33.0		35 x 41,0
55502449	SILVYN MPC M50	50 x 1.5	37.0		40 x 46,4
55502439	SILVYN MPC M63	63 x 1.5	48.0		50 x 57,2