


U.I. Lapp GmbH	PRODUCT INFORMATION	
	SKINTOP® SDV-M ATEX	12.09.2012

Permanent and secure sealing for areas with risks of explosion
Easy to assemble
High degree of protection



Application range

SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue).
Equipment group II / Category 2G+1D

Note

Outside areas with a risk of explosion, also suitable for use in combination with SKINTOP® ST-M and SKINTOP® MS-M

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Material:	CR
Protection rating:	IP 68 - sizes M12, M16, M20, M25, M32 IP 66 - sizes M40, M50, M63
Temperature range:	-30°C to +70°C Short-term: up to +90°C

Product Management	Document: LAPP_PRO995EN.pdf	1 / 2
--------------------	-----------------------------	-------

SKINTOP® SDV-M ATEX

12.09.2012

Part number	Article designation / size	Visible height (mm)
SKINTOP® SDV-M ATEX		
54113002	12 ATEX	SDV-M ATEX 3
54113012	16 ATEX	SDV-M ATEX 3
54113022	20 ATEX	SDV-M ATEX 3,5
54113032	25 ATEX	SDV-M ATEX 3,5
54113042	32 ATEX	SDV-M ATEX 4
54113052	40 ATEX	SDV-M ATEX 4
54113062	50 ATEX	SDV-M ATEX 4,5
54113072	63 ATEX	SDV-M ATEX 4,5