

Datasheet

Art.No. 96.031.1053.1

Female connector RST20I3F B2 M01 SW

Device connectors, standard M25, RST20i3, 3 pole, female, spring clamp connection, 250V/20A, color of coding: black, color of nut: black



Art.No.	96.031.1053.1
EAN	4015573743717
Order unit	1 pieces

Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Pollution degree	3
Mechanical coding	Yes
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	

Connection Data

Connection cross section solid	2.5 mm ²
Connection cross section stranded	1.5 mm ²
Terminations per pole	2

Model

Model	female
Number of poles	3
Connection type	Tension clamp connection
Connecting thread metric	M25
Angle of plug	Straight
Degree of protection (IP)	IP66/IP68
Remark to type of connection	Finely stranded con. req. Wieland cable end sleeve
Built-in component	Snap-in/screw-in

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn

Insulation components continuous temperature	100 °C
Surface finish	Silver-plated

Dimensions

Length	46.5 mm
Width	35 mm
Height	35 mm

