


Datasheet

Art.No. 57.506.9055.0

Earth terminal WK 6 SL / U / V0

Ground DIN rail terminal block with screw connection for mounting on TS 35 and TS 32, nominal cross section 6 mm², width 8 mm, color green/yellow



Art.No.	57.506.9055.0
EAN	4015573458635
Order unit	100 pieces

Approvals



Technical data

General

Nominal cross section	6 mm ²
Colour	Green/yellow
Number of levels	1
Number of clamp positions per level	2
Width/grid dimension	8 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Explosion-tested version "Ex e"	Yes
Mounting method	DIN rail (top hat rail)/G-rail
Terminal blocks for electrical installations	Yes

Technical data

Rated voltage	800 V
Rated impulse voltage	8 kV
Pollution degree	3
Closing plate required	No
Length	54 mm
Type of insulation material	Thermoplastic

Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	0.5 mm ²

Maximum cross section solid	10 mm ²
Minimum cross section fine stranded	0.5 mm ²
Maximum cross section fine stranded	6 mm ²
Wire strip length	12 mm
Torque conductor mounting	1.2 Nm
Torque rail mounting	1,2

Technical Data UL/CSA

Cross section UL	22-8 AWG
Cross section CSA	20-8 AWG

