



Rapid Part Number: **49-9439**
 Europa Part Number: **CSFL4U**
 Specifications and dimensions

- 4mm fuse link terminal
- Suitable for TS32 and TS35 din rail mounting



Features	
Length	43mm
Width	8mm
Depth	58mm
Weight	0.015Kg
Maximum cable connection	4mm ²
Rated voltage	800V
Rated current	6.3A
Tightening torque	0.5Nm
Construction	6-6 polyamide
Colour	Grey
Related products	
5X20 glass fuse quick blow	70-001-34
5X20 glass fuse medium blow	70-001-02
5X20 glass fuse slow blow	70-001-35
Copper link	CSFL4UCL
End plate	CSFLEPU
Partition plate	CTSP5U
End stop	CA702
Blank terminal marker half height	CA509/K2
Blank terminal marker	CA509/K6
Group marker	CA509/G1
Holding plate	CSP1
Protective cover 150mm	CTSPC
Group marker holder	GMH7

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
 website: <http://www.europacomponents.com>