

Product information

97 43 05

Crimp System Pliers

For exchangeable crimping dies



- With attached crimping dies for non-insulated open plug-type connectors (4.8 and 6.3 mm connector width)
- Just one tool for almost 1000 crimping applications
- Almost parallel crimping motion
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Ergonomically designed handles
- Different locators for precise positioning of the connectors
- Crimping dies for applications not covered in the range offered here, may be available on request
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 43 05
EAN	4003773031031
Pliers	burnished
Head	burnished
Handles	with multi-component grips
weight	618 g
Dimensions	200 x 96 x 17 mm
Reach	yes
RohS	no

Technical details



Applications	Crimp System Pliers for non-insulated open plug-type connectors (4.8 and 6.3 mm connector width)
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Accessories

97 49 95	Locator for 97 49 05
----------	----------------------

technical change and errors excepted