

## Product information

# 98 20 30

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

## Screwdrivers for slotted screws

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General	
Article No.	98 20 30
EAN	4003773062332
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	35 g
Dimensions	202 x 23 x 25 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no
Technical details	
Blade length	100 mm
Length of non-insulated blade	15 mm
Handle length	102 mm
Blade width	3.0 mm
Blade thickness	0.5 mm
VDE tested	yes
Classification	
eCl@ss 5.1.4	21040401
ETIM 5.0	EC000158
ETIM 6.0	EC000158
proficl@ss 6.0	AAA817c008
UNSPSC 13.1	27111701

technical change and errors excepted