

## Product information

# 98 24 03

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

## Screwdriver for cross recessed screws

Phillips®

IEC 60900 DIN EN 60900



⚡ 1000V ⚡

General	
Article No.	98 24 03
EAN	4003773026464
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	165 g
Dimensions	270 x 39 x 36 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no
Technical details	
Size	PH3
Blade length	150 mm
Handle length	120 mm
Blade dia.	8.0 mm
Length of non-insulated blade	18 mm
VDE tested	yes
Classification	
eCl@ss 5.1.4	21040401
ETIM 5.0	EC000144
ETIM 6.0	EC000144
proficl@ss 6.0	AAA818c006
UNSPSC 13.1	27111701

*technical change and errors excepted*

*Phillips® is a registered trademark of Phillips Screw Company*