

Product information

98 25 04

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for cross recessed screws

Pozidriv®

IEC 60900 DIN EN 60900



⚠ 1000 V ⚡

| General | |
|-------------------------------|---|
| Article No. | 98 25 04 |
| EAN | 4003773062387 |
| point | burnished |
| Handles | insulating multi-component handle, VDE-tested |
| weight | 245 g |
| Dimensions | 320 x 37 x 36 mm |
| Standard | DIN EN 60900 IEC 60900 |
| Reach | no |
| RohS | no |
| Technical details | |
| Size | PZ4 |
| Blade length | 200 mm |
| Handle length | 120 mm |
| Blade dia. | 10.0 mm |
| Length of non-insulated blade | 18 mm |
| VDE tested | yes |
| Classification | |
| eCl@ss 5.1.4 | 21040401 |
| ETIM 5.0 | EC000144 |
| ETIM 6.0 | EC000144 |
| proficl@ss 6.0 | AAA818c006 |
| UNSPSC 13.1 | 27111701 |

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.