

Product information

99 00 280

- To twist and cut wire in one operation: fast, reliable and economical
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

Concreters' Nipper

(Concreter's Nippers or Fixer's Nippers)

DIN ISO 9242



General

Article No.	99 00 280
EAN	4003773014096
Pliers	black atramentized
Head	polished
weight	455 g
Dimensions	280 x 48 x 22 mm
Standard	DIN ISO 9242
Reach	no
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 2.8
Cutting capacities hard wire (diameter)	Ø 1.8
Cutting edge length mm	25 mm

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC483c003

technical change and errors excepted



