

## Product information

# 87 01 560

### KNIPEX Cobra® XXL

#### Pipe Wrench and Water Pump Pliers

DIN ISO 8976



- Greater gripping capacity but much lower weight than comparable pipe wrenches
- Fast push-button adjustment directly on the workpiece, no unintentional slipping of the joint
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

### General

|             |                   |
|-------------|-------------------|
| Article No. | 87 01 560         |
| EAN         | 4003773044321     |
| Pliers      | grey atramentized |
| Head        | polished          |
| Handles     | plastic coated    |
| weight      | 2,780 g           |
| Dimensions  | 560 x 103 x 29 mm |
| Standard    | DIN ISO 8976      |
| Reach       | no                |
| RohS        | no                |

### Technical details

|                                 |              |
|---------------------------------|--------------|
| Adjustment positions            | 20           |
| Capacities for nuts             | Ø 4 1/2 Inch |
| Capacities for nuts             | 120 mm       |
| Capacities for pipes (diameter) | Ø 115 mm     |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| ETIM 5.0       | EC000164   |
| ETIM 6.0       | EC000164   |
| proficl@ss 6.0 | AAA936c004 |
| UNSPSC 13.1    | 27112112   |

*technical change and errors excepted*

