

## Product information

# 88 07 250

### KNIPEX Alligator®

#### Water Pump Pliers

DIN ISO 8976 IEC 60900 DIN EN 60900



⚡ 1000V 

- Good access to the workpiece due to slim size of head and joint area
- More output and comfort compared to conventional water pump pliers of the same length: 9-notch adjustment positioning for 30 % more gripping capacity
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Robust construction, insensitive to dirt; particularly suitable for outdoor work
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	88 07 250
EAN	4003773019343
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	420 g
Dimensions	250 x 82 x 32 mm
Standard	DIN ISO 8976 DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Adjustment positions	9
Capacity for pipes, inches (diameter)	Ø 2
Capacities for nuts	46 mm
Capacities for pipes (diameter)	Ø 50 mm
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112111

technical change and errors excepted

