

## Product information

**97 49 09**

- Application: insulated + non-insulated wire ferrules 10 / 16 / 25 mm<sup>2</sup>

## Crimping dies


For wire ferrules



### General

Article No.	97 49 09
EAN	4003773030881
weight	50 g
Dimensions	50 x 12 mm
Reach	no
RohS	no

### Technical details



Applications	insulated and non-insulated wire ferrules
Capacity in square millimetres	10 / 16 / 25 mm <sup>2</sup>
Number of crimping positions	3
AWG	7 / 5 / 3

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820

*technical change and errors excepted*