

## Product information

**97 49 04**

- Application: non-insulated open plug type connectors (plug width 2.8 + 4.8 mm) 0.1 - 2.5 mm<sup>2</sup>

### Crimping dies

For non-insulated open plug-type connectors 2.8 + 4.8 mm



#### General

Article No.	97 49 04
EAN	4003773030850
weight	42 g
Dimensions	50 x 10 mm
Reach	yes
RohS	no

#### Technical details



Applications	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 2.5 mm <sup>2</sup>
Number of crimping positions	4
AWG	27 — 13

#### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112820



**Accessories**

97 49 94

Locator for 97 49 04

*technical change and errors excepted*