

Product information


97 52 33

KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 52 33
EAN	4003773051862
Pliers	burnished
Handles	with multi-component grips
weight	478 g
Dimensions	220 x 59 x 30 mm
Reach	yes
RohS	no

Technical details	
	
Applications	non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	0.5 — 10.0 mm ²
Number of crimping positions	4
AWG	20 — 7

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted