

Product information


97 52 37

KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 52 37
EAN	4003773063193
Pliers	burnished
Handles	with multi-component grips
weight	478 g
Dimensions	220 x 70 x 21 mm
Reach	yes
RohS	no

Technical details	
	
Applications	heat shrinkable sleeve connectors
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted



97 52 37



97 52 37