

Product information

97 52 30

KNIPEX PreciForce® Crimping Pliers


- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened




General

Article No.	97 52 30
EAN	4003773051855
Pliers	burnished
Handles	with multi-component grips
weight	477 g
Dimensions	220 x 70 x 31 mm
Reach	yes
RohS	no

Technical details



Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	1.5 — 10.0 mm ²
Number of crimping positions	5
AWG	15 — 11



Applications	non-insulated crimp connectors in accordance with DIN 46267
Capacity in square millimetres	6.0 / 10.0 mm ²
Number of crimping positions	2
AWG	10 / 8

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

technical change and errors excepted