

## Product information

# 97 52 38

## KNIPEX PreciForce® Crimping Pliers


- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



### General

Article No.	97 52 38
EAN	4003773051909
Pliers	burnished
Handles	with multi-component grips
weight	493 g
Dimensions	220 x 58 x 21 mm
Reach	yes
RohS	no

### Technical details



Applications	insulated and non-insulated wire ferrules
Capacity in square millimetres	0.25 — 6.0 mm <sup>2</sup>
Number of crimping positions	5
AWG	23 — 10

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

*technical change and errors excepted*