

## Product information


# 97 52 50

## KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 52 50
EAN	4003773051916
Pliers	burnished
Handles	with multi-component grips
weight	498 g
Dimensions	220 x 70 x 21 mm
Reach	yes
RohS	no

Technical details	
	
Applications	Coax-, BNC- and TNC-connectors for RG 58/174/188/316
Number of crimping positions	6
Capacity SW mm	0.72 / 1.07 / 1.72 / 3.25 / 4.52 / 5.4 mm
Sleeves (diameter)	Ø 0.95 / 1.3 / 2.1 / 3.9 / 5.4 / 6.4 mm

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

*technical change and errors excepted*