

Product information

48 11 J0

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- Straight tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General

| | |
|-------------|-------------------------------|
| Article No. | 48 11 J0 |
| EAN | 4003773048510 |
| Pliers | grey atramentized |
| Handles | with non-slip plastic coating |
| weight | 105 g |
| Dimensions | 140 x 52 x 11 mm |
| Standard | DIN 5256 C |
| Reach | no |
| RohS | no |

Technical details

| | |
|-----------------|-------------|
| Style | 1 |
| Size of bore | Ø 8 – 13 mm |
| Tips (diameter) | Ø 0.9 mm |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC002228 |
| ETIM 6.0 | EC002228 |
| proficl@ss 6.0 | AAC470c002 |
| UNSPSC 13.1 | 27112140 |

technical change and errors excepted