

Product information

48 11 J4

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 C



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- Straight tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General

Article No.	48 11 J4
EAN	4003773048558
Pliers	grey atramentized
Handles	with non-slip plastic coating
weight	580 g
Dimensions	320 x 46 x 17 mm
Standard	DIN 5256 C
Reach	no
RohS	no

Technical details

Style	1
Size of bore	Ø 85 – 140 mm
Tips (diameter)	Ø 3.2 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted