

Product information


48 21 J31

Precision Circlip Pliers

For internal circlips in bore holes

DIN 5256 D

- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Bolted joint: precise, zero backlash operation of pliers
- Non-slip plastic coating on the handles
- Angled tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened



General

Article No.	48 21 J31
EAN	4003773048657
Pliers	grey atramentized
Handles	with non-slip plastic coating
weight	265 g
Dimensions	210 x 45 x 13 mm
Standard	DIN 5256 D
Reach	no
RohS	no

Technical details

Style	2
Size of bore	Ø 40 – 100 mm
Tips (diameter)	Ø 2.3 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted