

## Product information

# 70 06 125

## Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



### General

Article No.	70 06 125
EAN	4003773018124
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	121 g
Dimensions	125 x 55 x 18 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Cutting capacities soft wire (diameter)	Ø 3.0 mm
Cutting capacities medium hard wire (diameter)	Ø 2.3 mm
Cutting capacities hard wire (diameter)	Ø 1.5 mm
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

