

Product information

75 02 125

Electronics Diagonal Cutter

DIN ISO 9654

- Bolted joint for high precision and stress tolerance
- For ultra fine cutting work, e.g. in electronics and fine mechanics
- With sharp, ground cutting edges for soft and hard wire and piano wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Low-friction double spring for gentle and even opening
- With bevel
- High-grade special tool steel, forged, multi stage oil-hardened




General

Article No.	75 02 125
EAN	4003773043720
Pliers	burnished
Handles	with plastic grips
weight	80 g
Dimensions	125 x 74 x 17 mm
Standard	DIN ISO 9654
Reach	no
RohS	no

Technical details

Style	0
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.3 mm
	14 mm
	6.5 mm
Head width (A)	10.5 mm



Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted



Bolted joint