

Product information

70 02 140

Diagonal Cutter

DIN ISO 5749

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	70 02 140
EAN	4003773023098
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
weight	150 g
Dimensions	140 x 54 x 19 mm
Standard	DIN ISO 5749
Reach	no
RohS	no

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 2.5 mm
Cutting capacities hard wire (diameter)	Ø 1.8 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted

