

## Product information

# 01 06 160

### Combination Pliers

Chrome Vanadium

DIN ISO 5746 IEC 60900 DIN EN 60900

- For heavy duty
- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft, hard and piano wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Particularly wear resistant gripping jaws; hardness of the gripping jaws approx. 53 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



#### General

Article No.	01 06 160
EAN	4003773040729
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	220 g
Dimensions	160 x 55 x 20 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900
Reach	no
RohS	no

#### Technical details

Cutting capacities hard wire (diameter)	Ø 2.0 mm
Cutting capacities piano wire (diameter)	Ø 1.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 10.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm <sup>2</sup>
VDE tested	yes

#### Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

*technical change and errors excepted*