

## **Product information**

## 02 01 180

## **High Leverage Combination Pliers**

**DIN ISO 5746** 





- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile
  use
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

General	
Article No.	02 01 180
EAN	4003773033134
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	202 g
Dimensions	180 x 48 x 14 mm
Standard	DIN ISO 5746
Reach	no
RohS	no

Technical details	
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacities piano wire (diameter)	Ø 2.0 mm
Cutting capacity copper cable, multiple- stranded	Ø 11.5 mm
Cutting capacity copper cable, multiple- stranded	16.0 mm <sup>2</sup>

Classification	
eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted

## **KNIPEX** Quality – Made in Germany







