

## Product information

# 02 07 225

## High Leverage Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

### General

Article No.	02 07 225
EAN	4003773022305
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	486 g
Dimensions	225 x 71 x 35 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Cutting capacities hard wire (diameter)	Ø 3.0 mm
Cutting capacities piano wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 14.0 mm
Cutting capacity copper cable, multiple-stranded	25.0 mm <sup>2</sup>
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted