

Product information

03 01 200

Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General	
Article No.	03 01 200
EAN	4003773013259
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	276 g
Dimensions	200 x 43 x 14 mm
Standard	DIN ISO 5746
Reach	no
RohS	no
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacity copper cable, multiple-stranded	Ø 13.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²
Classification	
eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112139

technical change and errors excepted