

Product information

95 05 165

Cable Shears

Handles extrusion plastic-coated



- Cuts cables up to 10 mm dia. / 24 mm²
- With opening spring and locking device
- Blades made of stainless steel
- Oil-hardened and tempered
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- No crushing, slight deformation of the cable only
- Pinch guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof

MM

General	
Article No.	95 05 165
EAN	4003773019596
Head	polished
Handles	plastic coated
weight	111 g
Dimensions	165 x 48 x 16 mm
Reach	Nein
RohS	no
Technical details	
Cutting capacity copper cable, multiple-stranded	24 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 10 mm
AWG	4
Classification	
eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted