

Product information

95 31 280

Cable Cutter (ratchet action)



- Fixed handle with support area for putting down the pliers when cutting
- Suitable for aluminium sector cable up to 4 x 150 mm²
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

MM

| General | |
|--|----------------------------|
| Article No. | 95 31 280 |
| EAN | 4003773043942 |
| Pliers | black lacquered |
| Handles | with multi-component grips |
| weight | 860 g |
| Dimensions | 280 x 131 x 34 mm |
| Reach | yes |
| RohS | no |
| Technical details | |
| Cutting capacity copper cable, multiple-stranded | 380 mm ² |
| Cutting capacity copper cable, multiple-stranded | Ø 52 mm |
| MCM | 750 |
| Classification | |
| eCl@ss 5.1.4 | 21040301 |
| proficl@ss 6.0 | AAC484c002 |
| UNSPSC 13.1 | 23241616 |

technical change and errors excepted



95 31 250/280: fixed handle with support area as an aid to position the cutters on a flat surface



Ratchet principle and two-stage ratchet drive for easier cutting



95 31 280: Large cutting capacity: maximum 52 mm dia. / 380 mm²