

Product information

95 31 250

Cable Cutter (ratchet action)



- Fixed handle with support area for putting down the pliers when cutting
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

MM

General

Article No.	95 31 250
EAN	4003773043935
Pliers	black lacquered
Handles	with multi-component grips
weight	676 g
Dimensions	250 x 77 x 22 mm
Reach	yes
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	240 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 32 mm
MCM	500

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

technical change and errors excepted



