

## Product information

# 95 36 320

## Cable Cutter

(ratchet principle, 3-stage)

IEC 60900 DIN EN 60900



⚡ 1000 V 

- Sturdy. Easy to use. Stable.
- Innovative ratchet-drive.
- For cable up to 60 mm diameter.
- Fixed handle with support area for putting down the pliers when cutting
- Easy handling due to low weight (825 g) and compact construction (320 mm length) - also usable in confined areas
- Cutting through copper and aluminium cables with diameters of up to 60 mm in one-hand and two-hand operation
- Hardened, precision-ground cutting edges cut smoothly and neatly without crushing
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Innovative three-stage ratchet-drive with high leverage for easy cutting in one-hand and two-hand operation
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- High-grade special tool steel, forged, oil-hardened

### General

Article No.	95 36 320
EAN	4003773075189
Pliers	black atramentized
Head	polished
Handles	insulated with multi-component grips, VDE-tested
weight	830 g
Dimensions	320 x 188 x 39 mm
Standard	DIN EN 60900 IEC 60900
Reach	yes
RohS	no

### Technical details

Cutting capacity copper cable, multiple-stranded	600 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 60 mm
MCM	1,200
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

*technical change and errors excepted*

