

Product information

70 07 160

Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- With elongated cutting edge
- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



⚡ 1000 V 

General

| | |
|-------------|-------------------------------------|
| Article No. | 70 07 160 |
| EAN | 4003773018155 |
| Pliers | chrome plated |
| Head | chrome plated |
| Handles | with dipped insulation, VDE-tested |
| weight | 227 g |
| Dimensions | 160 x 60 x 28 mm |
| Standard | DIN ISO 5749 DIN EN 60900 IEC 60900 |
| Reach | no |
| RohS | no |

Technical details

| | |
|--|----------|
| Cutting capacities soft wire (diameter) | Ø 4.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 3.0 mm |
| Cutting capacities hard wire (diameter) | Ø 2 mm |
| VDE tested | yes |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1 | 27112114 |

technical change and errors excepted