

Product information

70 05 180

Diagonal Cutter

DIN ISO 5749

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



| General | |
|--|----------------------------|
| Article No. | 70 05 180 |
| EAN | 4003773043706 |
| Pliers | chrome plated |
| Head | chrome plated |
| Handles | with multi-component grips |
| weight | 246 g |
| Dimensions | 180 x 53 x 21 mm |
| Standard | DIN ISO 5749 |
| Reach | no |
| RohS | no |
| Technical details | |
| Cutting capacities soft wire (diameter) | Ø 4.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 3.0 mm |
| Cutting capacities hard wire (diameter) | Ø 2.5 mm |
| Classification | |
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1 | 27112114 |

technical change and errors excepted