

Product information

71 12 200

KNIPEX CoBolt®

Compact Bolt Cutters



Clever muscle man

- Micro-structured cutting edge reduces slipping of the material from the jaws
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- With slim multi-component grips without collar for better handling and easier transport
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

General

Article No.	71 12 200
EAN	4003773066859
Pliers	black atramentized
Handles	with slim multi-component grips
weight	375 g
Dimensions	200 x 62 x 24 mm
Reach	yes
RohS	no

Technical details

Style	1
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted

