

## Product information

# 71 22 200

## KNIPEX CoBolt®

### Compact Bolt Cutters



MM   $\angle 20^\circ$



#### Clever muscle man

- With slim multi-component grips without collar for better handling and easier transport
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

### General

Article No.	71 22 200
EAN	4003773066873
Pliers	black atramentized
Handles	with slim multi-component grips
weight	375 g
Dimensions	200 x 62 x 24 mm
Reach	no
RohS	no

### Technical details

Style	2
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted



20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping

