

Product information

71 21 200

KNIPEX CoBolt®
Compact Bolt Cutters



Clever muscle man

- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	71 21 200
EAN	4003773066866
Pliers	black atramentized
Handles	plastic coated
weight	320 g
Dimensions	200 x 62 x 24 mm
Reach	no
RohS	no

Technical details	
Style	2
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted

