

## Product information

# 71 31 200

## KNIPEX CoBolt® Compact Bolt Cutters



### Clever muscle man

- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- With recess for easier cutting of thicker wires
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- The recess in the blade allows easier cutting of thicker wires, e. g. for anchor bolts in false ceilings
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

Article No.	71 31 200
EAN	4003773042327
Pliers	black atramentized
Handles	plastic coated
weight	330 g
Dimensions	200 x 46 x 16 mm
Reach	yes
RohS	no

### Technical details

Style	3
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAC440c002
UNSPSC 13.1	27111512

technical change and errors excepted



the recess in the blade allows easier cutting of thicker wires, e. g. for anchor bolts in false ceilings