

Product information

71 41 200

KNIPEX CoBolt® Compact Bolt Cutters



Clever muscle man

- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Efficient joint design ensures exceptional cutting performance with little effort
- With recess for easier cutting of thicker wires
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- The recess in the blade allows easier cutting of thicker wires, e. g. for anchor bolts in false ceilings
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General	
Article No.	71 41 200
EAN	4003773066897
Pliers	black atramentized
Handles	plastic coated
weight	335 g
Dimensions	200 x 62 x 24 mm
Reach	yes
RohS	no

Technical details	
Style	4
Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27111512

technical change and errors excepted

