



2-conductor ground terminal block

Item No.: 285-197



2-conductor ground terminal block

Marking

RoHS
Compliant

Business data

Supplier	WAGO
Item no.	285-197
GTIN / EAN	4045454204372
Content	1

Notes

Technical data


Miscellaneous

Safety information 1	sively on DIN-35 x 15 rail; 2.3 mm thick, copper
Ratings per	IEC/EN 60947-7-2
Type of wiring	Side-entry wiring
Total number of connection points	2
Total number of potentials	1

Technical data	
<i>Number of levels</i>	1
<i>Connection technology</i>	POWER CAGE CLAMP
<i>Actuation type</i>	Operating tool
<i>Connectable conductor materials</i>	Copper
<i>Solid conductor</i>	25 ... 95 mm ² / 4 ... 4/0 AWG
<i>Fine-stranded conductor</i>	25 ... 95 mm ² / 4 ... 4/0 AWG
<i>Strip length</i>	35 mm / 1.38 Inch
<i>Width</i>	25 mm / 0.984 Inch
<i>Height from upper-edge of DIN-35 rail</i>	101 mm / 3.976 Inch
<i>Depth</i>	107 mm / 4.213 Inch
<i>Design</i>	horizontal
<i>Type of mounting</i>	Carrier rail 35 x 15
<i>Marking level</i>	Side marking
<i>Color</i>	green-yellow
<i>Insulating material</i>	Polyamide 66 (PA 66)
<i>Fire load [MJ]</i>	3.438 [MJ]
<i>Weight [g]</i>	309.278 [g]
<i>Product Family</i>	POWER CAGE CLAMP
<i>Main product function</i>	GND cond. term. block
<i>Product type</i>	High-current terminal blocks

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.