



## Multilevel installation terminal block; with N-disconnect slide link; NT/L/PE

Item No.: 2003-7641



### Marking

RoHS ✓  
Compliant

### Business data

Supplier	WAGO
Item no.	2003-7641
GTIN / EAN	4044918925587
Content	1

### Notes



### Technical data



#### Miscellaneous

Ratings note	potential - ground
Rated voltage (III / 3) [V]	250 [V]
Rated impulse voltage (III / 3) [kV]	4 [kV]
Rated current [A]	32 [A]
Ratings note 2	potential-potential

<b>Technical data</b>	
Rated voltage (III / 3) 2 [V]	400 [V]
Rated impulse voltage (III / 3) 2 [kV]	6 [kV]
Rated current (2) [A]	32 [A]
Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Type of wiring	Front-entry wiring
Total number of connection points	5
Total number of potentials	3
Number of levels	3
Connection technology	Push-in CAGE CLAMP®
Actuation type	Push-in
Connectable conductor materials	Copper
Nominal cross section	2.5 mm <sup>2</sup>
Solid conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Solid conductor, push-in termination	0.75 ... 4 mm <sup>2</sup> / 18 ... 12 AWG
Fine-stranded conductor	0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG
Fine-stranded conductor with ferrule, push-in termination, f	0.75 mm <sup>2</sup> / 18 AWG
Strip length	10 ... 12 mm / 0.39 ... 0.47 Inch
Width	5.2 mm / 0.205 Inch
Height from upper-edge of DIN-35 rail	42.3 mm / 1.665 Inch
Depth	96 mm / 3.78 Inch
Design	angled
Type of mounting	Carrier rail 35 x 15
Potential marking	NT/L/PE
Marking level	Center/side marking
Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load [MJ]	0.247 [MJ]
Weight [g]	16.7 [g]
Product Family	TOPJOB® S
Main product function	Multilevel install. term. block
Product type	Installation rail-mount terminal blocks

Images & drawings





**Address**

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.