



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

## Data

### Electrical data

Rated current (Ex e II)	12 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	14 A
---------------	------

### Geometrical Data

Width	12.9 mm / 0.508 inch
-------	----------------------



---

Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

---

#### Material Data

---

Color	light gray
Fire load	0.009 MJ
Weight	1.12 g

---

Subject to changes.