



RoHS Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

Data

Electrical data

Rated current (Ex e II)	12 A
-------------------------	------

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
Rated current	14 A

Geometrical Data

Width	30.5 mm / 1.201 inch
Height	19 mm / 0.748 inch



Depth	4.1 mm / 0.161 inch
-------	---------------------

Material Data

Color	light gray
-------	------------

Fire load	0.021 MJ
-----------	----------

Weight	2.61 g
--------	--------

Subject to changes.